

Fisherbrand™ Tyvek™ Cat III Coveralls

Fisherbrand Tyvek™ Hooded Coveralls are made from a soft and unique polyethylene nonwoven fabric, offering a great balance of protection and comfort.

Providing adequate Type 5 and 6 barrier protection, they remain permeable to both air and moisture vapour.

Fisherbrand Tyvek™ Cat III coveralls offer demonstrably more protection than equivalent SMS garments and are more robust than microporous films.

- Robust yet lightweight (less than 180g/garment)
- Elasticated face, wrists, waist and ankles
- Antistatic treatment on the outside
- Stitched external seams in yellow for visual identification and differentiation



Technical Specification

Certifications/Compliance	Type 5/6, (EU) 2016/425, EN 1073-2, EN 1149-5
Colour	White
Hood type	Two-piece
Product type	Hooded Coverall
Ankle style	Elastic
Material	PE (Polyethylene)
Seam type	Stitched
Available size	S, M, L, XL, 2XL, 3XL
Protection class	Category III, Type 5 and 6
Closure type	Zipper
Neck style	Hooded
Size (metric) chest	84 to 92cm (S) 92 to 100cm (M) 100 to 108cm (L) 108 to 116cm (XL) 116 to 124cm (2XL) 124 to 132cm (3XL)

Ordering Information

Cat. No	Description	Pack qty
16396515	Tyvek™ Fisherbrand Cat III coverall size S white	1
16306525	Tyvek™ Fisherbrand Cat III coverall size M white	1
16316525	Tyvek™ Fisherbrand Cat III coverall size L white	1
16326525	Tyvek™ Fisherbrand Cat III coverall size XL white	1
16336525	Tyvek™ Fisherbrand Cat III coverall size 2XL white	1
16346525	Tyvek™ Fisherbrand Cat III coverall size 3XL white	1

Austria: +43(0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
 Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
 Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
 Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
 Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500

© 2020 Thermo Fisher Scientific Inc. All rights reserved.
 Trademarks used are owned as indicated at fishersci.com/trademarks.